

Технические характеристики на профессиональные реометры Prescott Instruments

По вопросам продаж и поддержки обращайтесь:

Архангельск (8182)63-90-72
Брянск (4832)59-03-52
Вологда (8172)26-41-59
Иваново (4932)77-34-06
Калининград (4012)72-03-81
Киров (8332)68-02-04
Курск (4712)77-13-04
Москва (495)268-04-70
Нижний Новгород (831)429-08-12
Орел (4862)44-53-42
Пермь (342)205-81-47
Самара (846)206-03-16
Смоленск (4812)29-41-54
Тверь (4822)63-31-35
Тюмень (3452)66-21-18
Челябинск (351)202-03-61

Астана +7(7172)727-132
Владивосток (423)249-28-31
Воронеж (473)204-51-73
Ижевск (3412)26-03-58
Калуга (4842)92-23-67
Краснодар (861)203-40-90
Липецк (4742)52-20-81
Мурманск (8152)59-64-93
Новокузнецк (3843)20-46-81
Оренбург (3532)37-68-04
Ростов-на-Дону (863)308-18-15
Санкт-Петербург (812)309-46-40
Сочи (862)225-72-31
Томск (3822)98-41-53
Ульяновск (8422)24-23-59
Череповец (8202)49-02-64

Белгород (4722)40-23-64
Волгоград (844)278-03-48
Екатеринбург (343)384-55-89
Казань (843)206-01-48
Кемерово (3842)65-04-62
Красноярск (391)204-63-61
Магнитогорск (3519)55-03-13
Набережные Челны (8552)20-53-41
Новосибирск (383)227-86-73
Пенза (8412)22-31-16
Рязань (4912)46-61-64
Саратов (845)249-38-78
Ставрополь (8652)20-65-13
Тула (4872)74-02-29
Уфа (347)229-48-12
Ярославль (4852)69-52-93

Эл. почта: ptc@nt-rt.ru || Сайт: <http://prescott.nt-rt.ru/>

Multi-Function Rheometers are capable of fulfilling tasks of both a Moving Die Rheometer (MDR) and a Dynamic Shear Rheometer (DSR).

Modes of Operation:

- Frequency Sweep
- Temperature Sweep
- Strain Sweep
- Standard MDR Mode
- Conditioning
- Combination (Linked) Tests

Standards:

ISO 6502 / ISO 13145

ASTM D5289 / ASTM D6048 / ASTM D6204

ASTM D6601 / ASTM 7605

DIN 53529

Temperature Range:

Ambient to 250 °C


± 0.03 °C

Oscillation Frequency:

0.001 Hz to 50 Hz

Oscillation Amplitude:

± 0.001 ° to 360 °



Rheoline Multi-Function Rheometer Lite

Utilising a new generation In-line Servo Motor coupled with digital servo drive technology, the Rheoline Multi-Function Rheometer (MFR) Lite is complete with our Labline Lite software to ensure the highest standards precision of analytical and statistical data of elastomeric properties.

This dynamic rubber testing instrument is capable of fulfilling tasks of both a Moving Die Rheometer (MDR) and a Dynamic Shear Rheometer (DSR).

Software:

Labline Lite

Test Specifications:

(Max. 10)

Forced Cooling:

Optional Upgrade

Pressure Module:

Optional Upgrade

Rheoline Multi-Function Rheometer

Our most innovative dynamic testing rheometer is designed to deliver reliable results to the most precise accuracies with an extensive range of test stages or operations, capable of fulfilling tasks of both a Moving Die Rheometer and a Dynamic Shear Rheometer.

Provides vital analytical and statistical data of elastomeric properties, using our Labline software. This instrument comes complete with an Air Cooling System as standard to assist the operation of a Temperature Sweep. This is the ultimate choice for any polymer specialists.

Software
Labline

Test Specifications
(Unlimited)

Forced Cooling
Included

Pressure Module
Included

По вопросам продаж и поддержки обращайтесь:

Архангельск (8182)63-90-72
Брянск (4832)59-03-52
Вологда (8172)26-41-59
Иваново (4932)77-34-06
Калининград (4012)72-03-81
Киров (8332)68-02-04
Курск (4712)77-13-04
Москва (495)268-04-70
Нижегород (831)429-08-12
Орел (4862)44-53-42
Пермь (342)205-81-47
Самара (846)206-03-16
Смоленск (4812)29-41-54
Тверь (4822)63-31-35
Тюмень (3452)66-21-18
Челябинск (351)202-03-61

Астана +7(7172)727-132
Владивосток (423)249-28-31
Воронеж (473)204-51-73
Ижевск (3412)26-03-58
Калуга (4842)92-23-67
Краснодар (861)203-40-90
Липецк (4742)52-20-81
Мурманск (8152)59-64-93
Новокузнецк (3843)20-46-81
Оренбург (3532)37-68-04
Ростов-на-Дону (863)308-18-15
Санкт-Петербург (812)309-46-40
Сочи (862)225-72-31
Томск (3822)98-41-53
Ульяновск (8422)24-23-59
Череповец (8202)49-02-64

Белгород (4722)40-23-64
Волгоград (844)278-03-48
Екатеринбург (343)384-55-89
Казань (843)206-01-48
Кемерово (3842)65-04-62
Красноярск (391)204-63-61
Магнитогорск (3519)55-03-13
Набережные Челны (8552)20-53-41
Новосибирск (383)227-86-73
Пенза (8412)22-31-16
Рязань (4912)46-61-64
Саратов (845)249-38-78
Ставрополь (8652)20-65-13
Тула (4872)74-02-29
Уфа (347)229-48-12
Ярославль (4852)69-52-93