

Технические характеристики на вискозиметры Mooneyline Mini MV Lite Prescott Instruments



По вопросам продаж и поддержки обращайтесь:

Архангельск (8182)63-90-72
Брянск (4832)59-03-52
Вологда (8172)26-41-59
Иваново (4932)77-34-06
Калининград (4012)72-03-81
Киров (8332)68-02-04
Курск (4712)77-13-04
Москва (495)268-04-70
Нижний Новгород (831)429-08-12
Орел (4862)44-53-42
Пермь (342)205-81-47
Самара (846)206-03-16
Смоленск (4812)29-41-54
Тверь (4822)63-31-35
Тюмень (3452)66-21-18
Челябинск (351)202-03-61

Астана +7(7172)727-132
Владивосток (423)249-28-31
Воронеж (473)204-51-73
Ижевск (3412)26-03-58
Калуга (4842)92-23-67
Краснодар (861)203-40-90
Липецк (4742)52-20-81
Мурманск (8152)59-64-93
Новокузнецк (3843)20-46-81
Оренбург (3532)37-68-04
Ростов-на-Дону (863)308-18-15
Санкт-Петербург (812)309-46-40
Сочи (862)225-72-31
Томск (3822)98-41-53
Ульяновск (8422)24-23-59
Череповец (8202)49-02-64

Белгород (4722)40-23-64
Волгоград (844)278-03-48
Екатеринбург (343)384-55-89
Казань (843)206-01-48
Кемерово (3842)65-04-62
Красноярск (391)204-63-61
Магнитогорск (3519)55-03-13
Набережные Челны (8552)20-53-41
Новосибирск (383)227-86-73
Пенза (8412)22-31-16
Рязань (4912)46-61-64
Саратов (845)249-38-78
Ставрополь (8652)20-65-13
Тула (4872)74-02-29
Уфа (347)229-48-12
Ярославль (4852)69-52-93

Our Mini Mooneyline Viscometer **Lite** is a sleek and compact version of our Mooneyline Viscometer, supplied with everything you need to perform reliable and efficient elastomeric compound testing.

This entry level instrument features the same rotor and die assembly as our Mooneyline Viscometer, complete with a compact design that reduces instrument footprint. Thus making this ideal for the small to medium rubber testing laboratories.

The rotor rotates at a constant speed to two revolutions per minute and the torque is effectively measured and recorded.

In addition, the Mini Mooney meets the requirements of ASTM D1646 and can perform the following industry standard tests; **ML (1+X)** viscosity tests, **Scorch** testing and **Delta Mooney**.

Standards

ISO No. 289 / ASTM D1646

Test Capabilities

Mooney Torque or Mooney Scorch

Mini Viscometer is complete with everything you need to perform accurate and efficient elastomeric compound testing.

The provided PC comes pre-installed and calibrated with our data acquisition and analysis Labline Lite software.

- Microsoft Windows ® OS PC (Monitor, keyboard and mouse)
- Labline Lite Software
- All peripheral cables and connectors
- Essentials spares package
- Free technical support (one year)

Standards:	ISO No. 289 / ASTM D1646
Die Configuration:	Standard
Rotor:	Large or Small
Rotation Speed:	2 RPM (0.21 Radians/Sec)
Calibration:	Integral
Temperature Range:	Ambient to 225 °C
Temperature Control:	3 Term PID – Control Accuracy ± 0.03 °C
Pneumatics:	Filtered Air, Min: 0.41 MPa 60 psi 4.14 Bar 4.2 kg/cm
Electrical:	Single Phase 220/240 V 50 Hz 110 V 60 Hz 350 VA
Weight:	65 kg
Dimensions:	300 mm x 300 mm x 870 mm (W x D x H)

По вопросам продаж и поддержки обращайтесь:

Архангельск (8182)63-90-72
 Брянск (4832)59-03-52
 Вологда (8172)26-41-59
 Иваново (4932)77-34-06
 Калининград (4012)72-03-81
 Киров (8332)68-02-04
 Курск (4712)77-13-04
 Москва (495)268-04-70
 Нижний Новгород (831)429-08-12
 Орел (4862)44-53-42
 Пермь (342)205-81-47
 Самара (846)206-03-16
 Смоленск (4812)29-41-54
 Тверь (4822)63-31-35
 Тюмень (3452)66-21-18
 Челябинск (351)202-03-61

Астана +7(7172)727-132
 Владивосток (423)249-28-31
 Воронеж (473)204-51-73
 Ижевск (3412)26-03-58
 Калуга (4842)92-23-67
 Краснодар (861)203-40-90
 Липецк (4742)52-20-81
 Мурманск (8152)59-64-93
 Новокузнецк (3843)20-46-81
 Оренбург (3532)37-68-04
 Ростов-на-Дону (863)308-18-15
 Санкт-Петербург (812)309-46-40
 Сочи (862)225-72-31
 Томск (3822)98-41-53
 Ульяновск (8422)24-23-59
 Череповец (8202)49-02-64

Белгород (4722)40-23-64
 Волгоград (844)278-03-48
 Екатеринбург (343)384-55-89
 Казань (843)206-01-48
 Кемерово (3842)65-04-62
 Красноярск (391)204-63-61
 Магнитогорск (3519)55-03-13
 Набережные Челны (8552)20-53-41
 Новосибирск (383)227-86-73
 Пенза (8412)22-31-16
 Рязань (4912)46-61-64
 Саратов (845)249-38-78
 Ставрополь (8652)20-65-13
 Тула (4872)74-02-29
 Уфа (347)229-48-12
 Ярославль (4852)69-52-93

Эл. почта: ptc@nt-rt.ru || Сайт: <http://prescott.nt-rt.ru/>